TECHNICAL DATA SHEET



Duco Fast Dry Enamel

Product Description

Type: A single pack, synthetic resin based enamel

Recommended use: Repair and complete respray of cars, vans and commercial vehicles which require to have a hard wearing, durable finish.

Substrates: Suitably primed metal bodies.

Advantages: Fast drying. High opacity, good flow and gloss from the gun. Good exterior

durability

Conditions during application: The temperature of the substrate should be minimum 10°C and at least 3°C above the dew point of the air, measured near the substrate. Good ventilation is required in confined areas to ensure proper drying.

PRODUCT DATA:

Colour Range: A range of solid colours and toners plus clear.

Pack Sizes: ½ Litre, 1 litre and 4 litres

Finish: Gloss

Thinner & equipment cleaner: Fast Dry Thinner

Supply Viscosity: 128 – 132 KU @25°C.

Dry Film Thickness: $30 - 35 \mu m$.

Gloss: More than 80% @ 20° angle

Pencil Hardness: Passes 2H (after 24 hours)

APPLICATION DATA:

The product can be applied by: Spray.

Mixing Ratio: 4 parts Paint: 1 part Fast Dry Thinner (by volume)

Application Viscosity: 20 -22 seconds BS4 Cup @25°C

Application Pressure: 45 -50 PSI

Spreading Capacity per coat: Depends on film thickness applied, surface porosity, imperfections,

temperature & wastage during painting.

 $6-10 \text{ m}^2/1 \text{ per coat}$

Date of issue: 25/10/2019. Page: 1/3

TECHNICAL DATA SHEET



Drying time

Surface Temperature	Touch Dry	Handleable	Recoating & Hard Dry Time
15 − 25°C	2 hours	4 hours	24 hours
26 – 30°C	1¾ hours	3½ hours	16 hours
31 – 35°C	1 hour	3 hours	12 hours

For increased productivity, Fast Dry can be stoved at 60°C for 30 minutes with a flash off time of 10 minutes

Surface preparation & Paint System:

Surface	Preparation	Primer	Topcoat
New Mild Steel	Degrease. Repair dents. Sand with P80 – P120 sand paper	Duco Cellulose Primer Surfacer Grey	2 -3 coats Fast Dry Enamel
New Galvanised Iron, Aluminium & Fibreglass	Degrease. Repair dents. Sand with P80 – P120 sand paper 1 coat 1K Etch Primer	Duco Cellulose Primer Surfacer Grey	2 -3 coats Fast Dry Enamel
New wood	Ensure the wood is dry Sand along the grain with P320 sandpaper Dust off with cloth damped in thinner	Duco Cellulose Primer Surfacer Grey	2 -3 coats Fast Dry Enamel
Previously painted surfaces in sound condition	Remove loose paint Remove rust with rust remover Sand with P320-P400 sand paper	Duco Cellulose Primer Surfacer Grey	2 -3 coats Fast Dry Enamel

Availability: From Crown Depots in Nairobi, Kisumu, Mombasa, Meru, Nyeri, Eldoret, Arusha, Mwanza, Dar es Salaam, Kigali and through Crown Stockists.

Storage Conditions: Store under cool dry conditions away from direct sunlight, heat and extreme cold.

Disclaimer: The recommendations contained herein are given in good faith and meant to guide the user in accordance with good painting practices. They are gained from our tests and experiences and are believed to be accurate and reliable. No warranty/guarantee is implied by the recommendations contained herein since the conditions of use; application method, substrate and cleanliness of the substrate are beyond Crown Paints Kenya PLC control.

Technology may change with time, necessitating changes to this Technical Data Sheet (TDS). Crown Paints Kenya PLC reserves the right to amend the TDS without any further notice.

It is the responsibility of the user to ensure that the latest TDS is being used for reference.

TECHNICAL DATA SHEET









For additional health & safety information, please refer to our Material Safety Data Sheet (MSDS)